


BrightSign Zone Volume 0-100 減衰率対比表

Zone Volume 0-100	減衰率(dB)
100	0.0dB
94	-0.5dB
89	-1.0dB
84	-1.5dB
79	-2.0dB
75	-2.5dB
71	-3.0dB
67	-3.5dB
63	-4.0dB
60	-4.4dB
56	-5.0dB
53	-5.5dB
50	-6.0dB
47	-6.6dB
45	-6.9dB
42	-7.5dB
40	-8.0dB

Zone Volume 0-100	減衰率(dB)
38	-8.4dB
35	-9.1dB
33	-9.6dB
32	-9.9dB
30	-10.5dB
28	-11.1dB
27	-11.4dB
25	-12.0dB
24	-12.4dB
22	-13.2dB
21	-13.6dB
20	-14.0dB
19	-14.4dB
18	-14.9dB
17	-15.4dB
16	-15.9dB

Zone Volume 0-100	減衰率(dB)
15	-16.5dB
14	-17.1dB
13	-17.7dB
12	-18.4dB
11	-19.2dB
10	-20.0dB
9	-20.9dB
7	-23.1dB
6	-24.4dB
5	-26.0dB
4	-28.0dB
3	-30.5dB
2	-34.0dB
1	-40.0dB



感覚用フェーダ換算